

SHO-ME®

Strobe MicroDash

Model No. 20.1820

Electrical Specifications:

Output 20 Watts / 17 Joules
 Input Voltage 10-16 Volts
 Current Drain 2.0 Amps

Randomly Selected Flash Patterns

Single Flash	96 Single fpm
Double Flash	98 Double fpm
Triple Flash	87 Triple fpm
Quad Flash	70 Quad fpm
Mega Flash	260 Single fpm

Light Dimensions:

L 5.85" x H 1.75" x D 4.75" (Without bracket)



Bail Bracket



Windshield Bracket



Velcro Discs



Installation Instructions:

The mounting location will determine the type of bracket used. A windshield bracket is provided for mounting directly to the windshield. A bail bracket is included for mounting on dash or rear deck. The MicroDash Light may also be mounted without a bracket using the supplied Velcro discs. Install the bracket using the supplied hardware. **NOTE:** If you are using Velcro to mount the MicroDash Light, you must install the screws and washers to hold the flashback shield in place.

Windshield Mounting:

Choose the mounting location on windshield. The windshield bracket can be bent to allow for various windshield angles. **Clean the surface of the windshield with alcohol to ensure a proper bond.** Peel the backing strip off the 3M® adhesive tape which is pre-mounted to the bracket. Press firmly against windshield and hold for 5 seconds.



Bail Bracket Mounting:

The bail bracket can be used to mount the MicroDash Light in a variety of locations.



Velcro® Mounting:

Clean the surface of the MicroDash and the mounting surface with alcohol before applying discs. For correct alignment, press the hook and loop velcro discs together and adhere to the MicroDash Light first. Then put the MicroDash Light into the mounting position and press down against surface.



PRODUCTS COMPANY • 804 East Hwy. 248 • Cassville, MO 65625
 U.S. and Canada Toll Free Numbers • Phone: 800-641-4098 FAX: 800-526-1240
 E-mail: sales@able2products.com WEB: www.able2products.com

Wiring Instructions

The MicroDash Strobe Light has a 12' wire with a cigarette lighter plug and lighted switch. The plug contains a replaceable 8 amp fuse. To replace fuse, turn tip end of plug counterclockwise, then pull tip and fuse out.

After mounting the **SHO-ME**[®] 20.1820 MicroDash Light in desired location, route power wire to cigarette outlet, or power outlet. Keep in mind air bag deployment area and any other obstacles.

Linear Strobe Tube Replacement

Linear Strobe Tube part # 20.1880 can be replaced by removing the two screws that hold the lens in place. Remove the lens and pull out the strobe tube/ reflector assembly. Disconnect the strobe tube/ reflector assembly from the two connectors on the cable and plug in new assembly. Re-assemble in reverse order.

Replaceable polycarbonate lens part # 20.1885 is available in Clear, Blue, Red, Green, Amber and Purple.

LIMITED WARRANTY

Able 2 Products Company warrants each new product (except bulbs and strobe tubes) to be free from defects in material and workmanship for a period of two years from the date of purchase. During this warranty period, the obligation of Able 2 is limited to repairing or replacing, as Able 2 may elect, any part or parts, which after examination by Able 2 are determined to be defective, when they are delivered pre-paid. This limited warranty does not cover travel expense, the cost of specialized equipment for gaining access to the product, or labor charges for the removal and re-installation of the product.

Able 2 Products Company shall not be liable for incidental or consequential damages, including but not limited to: Loss of use of vehicle, Rental of substitute vehicle, Loss of time, Loss of work, Inconvenience, Transportation expenses, Telephone, Lodging, Loss of revenue, Loss of and/or damage to personal property for or arising out of breach of any express or implied warranty of its products.

Use of lamp or other electrical load of a wattage higher than installed or recommended by the factory, or use of inappropriate or inadequate wiring or circuit protection causes this limited warranty to become void. Able 2 Products Company will in no way be liable for any loss of profits or any indirect or consequential damages arising out of any such defect in material and workmanship whether loss is due to negligence or breach of warranty. This limited warranty does not apply to shipping damage, accident, alteration, tampering, misuse or abuse and unauthorized service.

This limited warranty is expressly in lieu of all other express or implied warranties, including the implied warranty of merchantability and the implied warranty of fitness for a particular purpose, and of all other obligations or liabilities on the part of Able 2 Products Company. There are no warranties, unless expressed in authorized Able 2 literature, which extend beyond the description of the face hereof. No dealer, distributor, employee, or representative of the company is authorized to change this warranty in any way or to grant any other warranty.

PRODUCT RETURNS

If a product must be returned, contact our factory by calling 1-800-641-4098 to obtain a Return Authorization Number (RA) before you ship the product. Write the RA Number clearly on the package and return it to Able 2 Products Company, P.O. Box 543, 804 E. Hwy. 248, Cassville, MO 65625-0543. A packing slip should be included with all shipments listing the sender's name, address, daytime phone number and description of defect. Your product will be put in first-class operating condition or replaced with a new part, and returned pre-paid.



PRODUCTS COMPANY • 804 East Hwy. 248 • Cassville, MO 65625
U.S. and Canada Toll Free Numbers • Phone: 800-641-4098 FAX: 800-526-1240
E-mail: sales@able2products.com WEB: www.able2products.com