

Model No. 12.3810 / 12.3812 Headlight Covert LED Kit 12-24VDC

Kit Installation

- 1. Remove the Headlight from vehicle.
- 2. Select location to mount lighthead.
- 3. Drill 1 inch diameter hole in the light assembly.
- 4. Insert lighthead into hole and secure with supplied screws.
- 5. Apply silicone (user-supplied) for better seal.

WARNING: DO NOT cover heat sink with silicone. It may cause damage to the product and void warranty.

Flash Patterns

- Single Flash 120 FPM all I FDs
- Single Flash 120 FPM ½ LEDs
- Single Flash 120 FPM alternating 1/2-1/2 LEDs
- Single Flash 300 FPM all LEDs Single Flash 300 FPM ½ LEDs
- Single Flash 300 FPM alternating 1/2-1/2 LEDs
- Single Flash 75 FPM all LEDs Single Flash 75 FPM ½ LEDs
- Single Flash 75 FPM alternating ½-½ LEDs
- Double Flash 75 FPM all LEDs
- Double Flash 75 FPM alternating 1/2-1/2 LEDs
- Double Flash 120 FPM all LEDs
- Quad Flash 120 FPM all LEDs
- Quad Flash 75 FPM all LEDs Quad Flash 75 FPM - 1/2 LEDs Quad Flash 75 FPM - alternating 1/2-1/2 LEDs

Double 120 FPM - alternating 1/2-1/2 LEDs


- Quad Flash 120 FPM 1/2 LEDs
- Quad Flash 120 FPM alternating ½-½ LEDs Quint Flash 120 FPM all LEDs 20.
- Quint Flash 120 FPM alternating 1/2-1/2 LEDs
- Alternating Module Flash 1/2-1/2
- Auto Run
- Steady Burn

Wiring instructions


Red to +VDC (fuse @ 3A) 12ft Cable Black to Chassis Ground White to +VDC Momentary

- 1. Syncing Configure LED's to the same Ph-1 pattern and connect blue wires together.
- 2. Alternating After setting desired pattern, unplug (1) light. With light unplugged, apply positive to yellow wire on remaining light to select Ph-2. Re-connect light. LED's should now flash in the same alternating pattern.

Note: If lightheads become out of sync, repeat steps 1 & 2.



NOTE: Mounting location may vary depending on the design of the vehicle light assembly.





PRODUCTS COMPANY • 804 East Hwy. 248 • Cassville, MO 65625 U.S. and Canada Toll Free Numbers • Phone: 800-641-4098 FAX: 800-526-1240 E-mail: sales@able2products.com WEB: www.able2products.com