

SHO-ME®

Model No. 25.4802

Installation Instructions for Gun-Lock Timer

General:

The **SHO-ME® Gun Lock Timer** provides easier, safer, and quicker use of all makes of electric gun locks by making shotgun removal a one-hand operation.

The gun-lock release switch normally connected to the lock is connected to both the lock and the timer. The gun-lock and timer are activated by pressing a momentary switch (switch included). The momentary switch does **not** need to be held in the down position. Since the timer allows power to be supplied for **8 seconds**, the same hand used for operating the switch is now free to remove or help remove the shotgun.

Timer failure from overload or short-circuit **will not prevent** normal, untimed release.

Before attempting installation of the timer, install the switch in a convenient operating position and proceed with the following timer installation.

Instructions

1. Connect the **black** timer wire to vehicle chassis ground. (-)
2. Connect the **white** timer wire to wire leading from switch to Gun-Lock.
3. Connect the **red** timer wire to the positive (+) terminal of the battery.
4. Connect the other switch terminal to the positive (=) terminal of the battery.
5. Using 12" tie-wrap secure the timer to a rigid vehicle component.

If the **Gun-Lock Timer** does not perform properly, check for proper wiring.
Remember: The timer will be activated for **8 seconds**.

LIMITED WARRANTY

Able 2 Products Company warrants each new product (except bulbs, strobe power supplies, and strobe tubes) to be free from defects in material and workmanship for a period of two years from the date of purchase. (Power Supplies - 5 yrs.—Strobe Tubes - 1 yr. - Halogen and Incandescent Bulbs no warranty) During this warranty period, the obligation of Able 2 is limited to repairing or replacing, as Able 2 may elect, any part or parts, which after examination by Able 2 are determined to be defective, when they are delivered pre-paid. This limited warranty does not cover travel expense, the cost of specialized equipment for gaining access to the product, or labor charges for the removal and re-installation of the product.

Able 2 Products Company shall not be liable for incidental or consequential damages, including but not limited to: Loss of use of vehicle, Rental of substitute vehicle, Loss of time, Loss of work, Inconvenience, Transportation expenses, Telephone, Lodging, Loss of revenue, Loss of and/or damage to personal property for or arising out of breach of any express or implied warranty of its products.

Use of lamp or other electrical load of a wattage higher than installed or recommended by the factory, or use of inappropriate or inadequate wiring or circuit protection causes this limited warranty to become void. Able 2 Products Company will in no way be liable for any loss of profits or any indirect or consequential damages arising out of any such defect in material and workmanship whether loss is due to negligence or breach of warranty. This limited warranty does not apply to shipping damage, accident, alteration, tampering, misuse or abuse and unauthorized service.

This limited warranty is expressly in lieu of all other express or implied warranties, including the implied warranty of merchantability and the implied warranty of fitness for a particular purpose, and of all other obligations or liabilities on the part of Able 2 Products Company. There are no warranties, unless expressed in authorized Able 2 literature, which extend beyond the description of the face hereof. No dealer, distributor, employee, or representative of the company is authorized to change this warranty in any way or to grant any other warranty.

PRODUCT RETURNS

If a product must be returned, contact our factory by calling 1-800-641-4098 to obtain a Return Authorization Number (RA) before you ship the product. Write the RA Number clearly on the package and return it to Able 2 Products Company, P.O. Box 543, 804 E. Hwy. 248, Cassville, MO 65625-0543. A packing slip should be included with all shipments listing the sender's name, address, daytime phone number and description of defect. Your product will be put in first-class operating condition or replaced

2/04

SHO-ME®

WIRING DIAGRAM FOR MODEL 25.4802 GUN-LOCK TIMER

